



SU212



**Bell 12V**

**Technical characteristics**

**Functions**

Mode of operation	Sound signal : type D - duration of intermittent operation recommended : 5s ON / 15s OFF
-------------------	--

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Rated operational voltage Ue	8 / 12 V
Type of supply voltage	AC

**Electric current**

Operating current	0.33 A
Rated current	0.33 A

**Dimensions**

Depth of installed product	65 mm
Height of installed product	80 mm
Width of installed product	18 mm

**Frequency**

Frequency	50 to 0 Hz
-----------	------------

**Power**

Power consumed	5 VA
Total power loss under IN	5 W

**Materials**

Material	polyamide
----------	-----------

**Connection**

Connection cross-sect. flexible conductor	4mm <sup>2</sup>
Connection cross-sect. rigid cable	6mm <sup>2</sup>

**Equipment**

Noise level	85 dB
-------------	-------

**Use conditions**

Operating temperature	-10...40 °C
Storage/transport temperature	-25...60 °C