



SU213



Bell 230V

Technical characteristics

Functions

Mode of operation

Sound signal : type D - duration of intermittent operation recommended : 5s ON / 15s OFF

Configuration

Number of modules

1

Main electrical features

Rated operational voltage U_e

230 V

Type of supply voltage

AC

Electric current

Operating current

0.03 A

Rated current

0.03 A

Dimensions

Depth of installed product

65 mm

Height of installed product

80 mm

Width of installed product

18 mm

Frequency

Frequency

50 to 0 Hz

Power

Power consumed

6.5 VA

Total power loss under IN

6.5 W

Materials

Material

polyamide

Connection

Connection cross-sect. flexible conductor

4mm²

Connection cross-sect. rigid cable

6mm²

Equipment

Noise level

85 dB

Safety

REACH conform

No

Use conditions

Operating temperature

-10...40 °C

