



SU213



## Bell 230V

### Technical characteristics

#### Architecture

Fixing mode DIN rail type O (symmetrical)

#### Configuration

Number of modules 1

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Type of supply voltage AC

#### Electric current

Operating current 0.03 A

Rated current 0.03 A

#### Dimensions

Depth of installed product 65 mm

Height of installed product 80 mm

Width of installed product 18 mm

#### Frequency

Frequency 50 to 0 Hz

#### Power

Power consumed 6.5 VA

Total power loss under IN 6.5 W

#### Materials

Material polyamide

#### Equipment

Noise level 85 dB

#### Standards

European directive WEEE concerned

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -10...40 °C

Storage/transport temperature -25...60 °C