



SU215



## Buzzer 230V

### Technical characteristics

#### Functions

Mode of operation	Sound signal : type D - duration of intermittent operation recommended : 5s ON / 15s OFF
-------------------	--

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage Ue	230 V
Type of supply voltage	AC

#### Electric current

Operating current	0.03 A
Rated current	0.03 A

#### Dimensions

Depth of installed product	65 mm
Height of installed product	80 mm
Width of installed product	18 mm

#### Frequency

Frequency	50 to 0 Hz
-----------	------------

#### Power

Power consumed	6.5 VA
Total power loss under IN	6.5 W

#### Materials

Material	polyamide
----------	-----------

#### Connection

Connection cross-sect. flexible conductor	4mm <sup>2</sup>
Connection cross-sect. rigid cable	6mm <sup>2</sup>

#### Equipment

Noise level	78 dB
-------------	-------

#### Use conditions

Operating temperature	-10...40 °C
Storage/transport temperature	-25...60 °C