



TJA510

IK04  IP20

Access Gate 2D/IP gateway DIN-rail

Technical characteristics

Functions

Function	Local and remote connection of the door station with IP end devices, such as smartphone, tablet computer and PC
Function	converting

Configuration

Number of modules	6
-------------------	---

Controls and indicators

Indication / display	image memory function, protocols visitors for display on Touch indoor station video comfort and IP end devices
Manual selection switches / push-buttons	Selection switch for online/offline mode

Connectivity

Connectors / jacks	with 2 USB sockets type A
IP	Integration of IP cameras into the 2-wire system

Voltage

Operating voltage	21.6 ... 33 V= or 48 V= Power over Ethernet PoE according to IEEE802.3
-------------------	--

Electric current

Current consumption (operation)	0.5 A
Making current	max. 650 mA

Dimensions

Width of rail mounted device (RMD)	6 modules
------------------------------------	-----------

Materials

Material	plastic
Surface appearance	mat

Connection

Type of connection	with QuickConnect plug-in terminals
Connection	with two RJ45 jacks

Scope of delivery

Component	with terminator
-----------	-----------------

Use

System technology	2-wire
-------------------	--------

Software

Update	Software update and downloads via USB interfaces on the device
--------	--

Software	Configuration with Hager Pilot as well as web browser from IE11, Chrome 32, Firefox 27, Edge 20
----------	---

Safety

Degree of contamination	2
-------------------------	---

Protection class	isol.class II
------------------	---------------

Protection	increased safety management
------------	-----------------------------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Altitude	< 2000 m
----------	----------

Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

Relative humidity (without condensation)	85 % at 25 °C
--	---------------

Instructions

Information text	App for iOS from version 10.2 and Android from version 5 can be downloaded free of charge from the corresponding app store
------------------	--
