



TJA510

IK04 IP20

Access Gate 2D/IP gateway DIN-rail

Technical characteristics

Architecture

Fixing mode DIN rail type O (symmetrical)

Functions

Function converting

Configuration

Number of modules 6

Controls and indicators

Manual selection switches / push-buttons Selection switch for online/offline mode

Connectivity

Connectors / jacks with 2 USB sockets type A

IP Integration of IP cameras into the 2-wire system

Voltage

Operating voltage 21.6 ... 33 V= or 48 V= Power over Ethernet PoE according to IEEE802.3

Electric current

Current consumption (operation) 0.5 A

Making current max. 650 mA

Dimensions

Width of rail mounted device (RMD) 6 modules

Materials

Material plastic

Surface appearance matt

Use

System technology 2-wire

Safety

Degree of contamination 2

Protection index IP IP20

Protection class isol.class II

Use conditions

Operating temperature -5...45 °C

Storage/transport temperature -25...70 °C (storage at > 45°C reduces the service life)

Instructions

Information text

App for iOS from version 10.2 and Android from version 5 can be downloaded free of charge from the corresponding app store