




TU404



4-channel remote control

Technical characteristics

Architecture

Number of keys	4
----------------	---

Functions

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
Function	easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control ; reset function (to factory setting)
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Controls and indicators

Button / push-button	with configuration button ; with side locking buttons
----------------------	---

Connectivity

Radio protocol	KNX Radio
AM / FM Modulation	FM
Receiver category	2

Dimensions

Depth of installed product	15.8 mm
Height of installed product	83 mm
Dimensions (LLxwxhh)	83 x 46,5 x 15,8 mm
Width of installed product	46.5 mm

Frequency

Transmission frequency	868 MHz
Radio transmission frequency	868.3 MHz

Power

Radio transmission power	< 10 mW
--------------------------	---------

Reach distance

Max. transmission range	30m in house / 100m free field
-------------------------	--------------------------------

Battery

life of battery	5 years
Battery / storage battery	with 2 x lithium coin cell battery 3 V type: CR 2430

LED control

LED	with configuration LED ; with transmission status and battery status LED, red/green/orange
-----	--

Connection

Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
----------------	--

Equipment

Number of radio channels	4
--------------------------	---

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Safety

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Key	with keyring
-----	--------------

Use conditions

Operating temperature	-10...45 °C
-----------------------	-------------

Energy-saving	low intrinsic energy requirement
---------------	----------------------------------