





TU406



6-channel remote control

Technical characteristics

Functions

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Dimensions

Depth of installed product	16 mm
Height of installed product	133.6 mm
Dimensions (LLxwxhh)	133,6 x 50,2 x 16 mm
Width of installed product	50.2 mm

Frequency

Transmission frequency	868 MHz
Radio transmission frequency	868.3 MHz

Power

Radio transmission power	< 10 mW
--------------------------	---------

Equipment

Number of radio channels	6
--------------------------	---

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Safety

Protection index IP	IP30
---------------------	------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------