



TXA210N

Dimmer 1 channel 600W

Technical characteristics

Architecture

Bus system	KNX
Fixing mode	Din-Rail

Configuration

Number of modules	4
-------------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Frequency	50/60 Hz
Rated current	2.6 A

Voltage

System supply voltage	30V DC via bus
-----------------------	----------------

Power

Incandescent bulb power	20 / 600 W
Total power loss under IN	4.8 W
Power of the variator	0 / 600 W

Materials

Colour	stone grey
--------	------------

Fluorescent bulbs control

Power lighting fluo lamps	120W
---------------------------	------

LED control

Power LED	120 W
-----------	-------

Connection

Type of load	universal
Type of connection	quick connect

Equipment

Type of dimmer	universal
Bidirectional radio frequency	No

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C