



TYF130

**Line coupler, KNX**

**Technical characteristics**

**Architecture**

Bus system EIB

**Functions**

Easy link functions can be used as line amplifier

**Configuration**

Number of modules 2

**Controls and indicators**

Button / push-button with programming button and red programming LED

**Voltage**

Operating voltage over bus 21...32 V DC

System supply voltage 30V DC via bus

**Dimensions**

Width of rail mounted device (RMD) 2 modules

**Power**

Total power loss under IN 0.5 W

**LED control**

LED with 2 yellow data traffic LEDs for higher and lower ranking line ; With green operation LED, red programming LED and red diagnosis LED

**Connection**

Type of connection to the bus TG008 connector

Bus coupling unit with integral bus coupling unit

Type of connection line connection via connecting terminal

Bus connection bus connection via connecting terminal

**Settings**

Supported configuration modes system, easy

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

Operating temperature -5...45 °C

