



TYF130



Line coupler, KNX

Technical characteristics

Architecture

Fixing mode Din-Rail

Functions

Easy link functions can be used as line amplifier

Configuration

Number of modules 2

Controls and indicators

Button / push-button with programming button and red programming LED

Voltage

Operating voltage over bus 21...32 V DC

System supply voltage 30V DC via bus

Dimensions

Width of rail mounted device (RMD) 2 modules

Power

Total power loss under IN 0.5 W

Connection

Type of connection to the bus TG008 connector

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

Settings

Supported configuration modes system

Use conditions

Operating temperature -5...45 °C

Identification

Main design line KNX