



UDBSQ06

British Standard screed floor Box

Technical characteristics

Architecture

Cable outlet Without cable outlet in cover

Dimensions

| | |
|----------------------------|--------|
| Minimal installation depth | 61 mm |
| External length | 289 mm |
| Internal length | 273 mm |
| Internal width | 273 mm |
| Thickness of carpet recess | 8 mm |
| External width | 289 mm |

Cover, door

Material Cover Polyamide

Materials

| | |
|---------------------------|-----------------------|
| Colour | light grey |
| RAL colour | RAL 7035 - Light grey |
| Material | Plastic/metal |
| Type of surface treatment | Structured |

Installation, mounting

| | |
|--------------------------|-----|
| Suitable for outdoor use | No |
| Installation on concrete | Yes |

Connection

Number of conduit inlets 8

Equipment

| | |
|-----------------------------|---|
| Amount of outlet boxes | 3 |
| Number of UK BS1363 sockets | 2 |

Use conditions

Maximum load Inspection stamp Ø 13mm 3 kN / Inspection stamp Ø 130mm 5 kN