



VT08TF

Flush transparent plastic flap 8M(ME&AF)

Technical characteristics

Configuration

Number of modules	8
-------------------	---

Compatibility

Suitable for lightning protection	Yes
-----------------------------------	-----

Dimensions

Insertion depth	80 mm
Depth of wall niche	80 mm
Depth of installed product	13 mm
Internal depth	79 mm
Height of installed product	253 mm
Width of installed product	316 mm
Width in division units	8
Thickness of sidewall material	1 mm
Built-in width	277 mm

Cover, door

Material thickness cover	1 mm
Identification od protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door leave	single
Transparent cover or door	Yes

Materials

Copper weight of the product	0 kg
Colour	light grey
Material	Mixed materials
Surface appearance	matt
Type of surface treatment	Painted

Installation, mounting

Suitable for outdoor use	No
Suitable for ground mounting	No

Equipment

Number of rows	1
Number of keys	1

Quantity of rails	1
On/Off switch	No
Number of openings for flange plates	0
Extension possible	No
Safety	
Protection index IP	IP40
Protection class	isol.class I
Glow wire test	according to IEC 61439-1
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Fire resistance	-