



VT08TS

## Technical characteristics

### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 8 |
|-------------------|---|

### Compatibility

|                                   |     |
|-----------------------------------|-----|
| Suitable for lightning protection | Yes |
|-----------------------------------|-----|

### Main electrical features

|                 |                |
|-----------------|----------------|
| Nominal voltage | 230 / 415 V AC |
|-----------------|----------------|

### Dimensions

|                                |        |
|--------------------------------|--------|
| Insertion depth                | 80 mm  |
| Depth of installed product     | 93 mm  |
| Internal depth                 | 79 mm  |
| Height of installed product    | 253 mm |
| Width of installed product     | 316 mm |
| Width in division units        | 8      |
| Thickness of sidewall material | 1 mm   |

### Cover, door

|                                    |                |
|------------------------------------|----------------|
| Material thickness cover           | 1 mm           |
| Identification od protection index | 40             |
| Interlockable                      | No             |
| Number of keylock of the door      | 0              |
| Cover type                         | Closed (plain) |
| Door leave                         | single         |
| Cover type                         | Cover          |
| Transparent cover or door          | Yes            |

### Materials

|                              |              |
|------------------------------|--------------|
| Copper weight of the product | 0 kg         |
| Material quality             | Material mix |
| Surface appearance           | matt         |
| Type of surface treatment    | Painted      |

### Installation, mounting

|                              |    |
|------------------------------|----|
| Suitable for outdoor use     | No |
| Suitable for ground mounting | No |

### Settings

|                |                           |
|----------------|---------------------------|
| Enclosure type | Distributor empty cabinet |
|----------------|---------------------------|

| <b>Equipment</b>                     |    |
|--------------------------------------|----|
| Number of rows                       | 1  |
| Number of keys                       | 1  |
| Quantity of rails                    | 1  |
| On/Off switch                        | No |
| Number of openings for flange plates | 0  |
| Extension possible                   | No |

#### **Standards**

|           |               |
|-----------|---------------|
| Approvals | BS EN 61439-3 |
|-----------|---------------|

#### **Safety**

|   |                          |
|---|--------------------------|
| IK protection code against mechanical impacts | IK05                     |
| Protection class                              | isol.class I             |
| Glow wire test                                | according to IEC 61439-1 |
| REACH conform                                 | Yes                      |
| RoHS conform                                  | Yes                      |
| Halogen free                                  | No                       |
| Fire resistance                               | -                        |