



WDW071

IP20

Flush-mounted housing for WDI07x, flush with wall

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

Touch function No

Connectivity

Connection RJ45 cable in scope of delivery

Dimensions

Cavity wall opening (W x H x D) 197.7 x 133.6 x 74 mm

Power

Total power loss under IN 0 W

Dissipated energy in cable 0 W

Screen

Display no

Materials

RAL colour RAL 7016 - Anthracite grey

Material Steel

Material family Metal

Installation, mounting

Installation mode for flush-mounted and hollow-wall mounting, for vertical and horizontal mounting

Equipment

Text field No

Safety

Protection index IP IP20

Use conditions

Storage/transport temperature -20...60 °C

Relative humidity (without condensation) 10...90 %

Identification

Composition other

Main design line KNX