



WDW100

IP20

Housing flush-mounted for WDI10x

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

Touch function	No
----------------	----

Connectivity

Connection	RJ45 cable in scope of delivery
------------	---------------------------------

Dimensions

Cavity wall opening (W x H x D)	260 x 177 x 64 mm
---------------------------------	-------------------

Power

Total power loss under IN	0 W
Dissipated energy in cable	0 W

Screen

Display	no
---------	----

Materials

RAL colour	RAL 7016 - Anthracite grey
Material	Steel
Material family	Metal

Installation, mounting

Installation mode	for flush-mounted and hollow-wall mounting, for vertical and horizontal mounting
-------------------	--

Equipment

Text field	No
------------	----

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	with cleaning cover

Use conditions

Storage/transport temperature	-20...60 °C
Relative humidity (without condensation)	10...90 %

