



WDW101

IP20

Flush-mounted housing for WDI10x, flush with wall

Technical characteristics

Functions

Touch function	No
----------------	----

Function	with Push-to-open mechanism for comfortable mounting
----------	--

Controls and indicators

Operation	depending on the software visualisation one and two surface operation, stepless configuration based on sliding and page scrolling by swiping are supported
-----------	--

Connectivity

Connection	RJ45 cable in scope of delivery
------------	---------------------------------

Connectors / jacks	with USB/Mini USB type A adapter cable ; with RJ45 connector kit from connector and patch cable
--------------------	---

Dimensions

Cavity wall opening (W x H x D)	269 x 186 x 74 mm
---------------------------------	-------------------

Power

Total power loss under IN	0 W
---------------------------	-----

Dissipated energy in cable	0 W
----------------------------	-----

Screen

Display	no
---------	----

Materials

Material family	Metal
-----------------	-------

Installation, mounting

Installation mode	for flush-mounted and hollow-wall mounting ; for vertical and horizontal mounting
-------------------	---

Scope of delivery

Component	Microphone and loudspeaker with echo suppression
-----------	--

Equipment

Interface type	other
----------------	-------

Text field	No
------------	----

Lighting	Display illumination can be switched on automatically using brightness sensor
----------	---

low noise	silent, long-lasting convection cooling without fan
-----------	---

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
Halogen free	Yes
Protection	with cleaning cover
Use conditions	
Storage/transport temperature	-20...60 °C
Relative humidity (without condensation)	10...90 %
Identification	
Composition	other
Main design line	KNX