

No

other



WDW101

IP20

Flush-mounted housing for WDI10x, flush with wall

Technical characteristics

Functions		
Touch function		

with Push-to-open mechanism for comfortable Function mounting

Controls and indicators

depending on the software visualisation one and two surface operation, stepless configuration based on Operation sliding and page scrolling by swiping are supported

Connectivity

Connection	RJ45 cable in scope of delivery
	with USB/Mini USB type A adapter cable ; with RJ45
Connectors / jacks	connector kit from connector and patch cable

Dimensions

Cavity wall opening (W x H x D) 269 x 186 x 74 mm

Power

Total power loss under IN	0 W
Dissipated energy in cable	0 W

Screen

Display

Materials

Material family Metal

Installation, mounting

for flush-mounted and hollow-wall mounting ; for Installation mode vertical and horizontal mounting

Scope of delivery

Component Microphone and loudspeaker with echo suppression

Equipment

Interface type

Text field No

Display illumination can be switched on automatically using brightness sensor

low noise silent, long-lasting convection cooling without fan

Safety

REACH conform Yes

RoHS conform	Yes
Halogen free	Yes
Protection	with cleaning cover
Use conditions	
Storage/transport temperature	-2060 °C
Relative humidity (without condensation)	1090 %
Identification	
Composition	other
Main design line	KNX