



WDW160

IP20

Housing flush-mounted for WDI16x

Technical characteristics

Functions

Touch function No

Controls and indicators

Operation depending on the software visualisation one and two surface operation, stepless configuration based on sliding and page scrolling by swiping are supported

Connectivity

Connection RJ45 cable in scope of delivery

Connectors / jacks with USB/Mini USB type A adapter cable ; with RJ45 connector kit from connector and patch cable

Dimensions

Cavity wall opening (W x H x D) 378 x 233 x 64 mm

Power

Total power loss under IN 0 W

Dissipated energy in cable 0 W

Screen

Display no

Materials

Material family Metal

Installation, mounting

Installation mode for flush-mounted and hollow-wall mounting ; for vertical and horizontal mounting

Scope of delivery

Component Microphone and loudspeaker with echo suppression

Equipment

Interface type other

Text field No

Lighting Display illumination can be switched on automatically using brightness sensor

low noise silent, long-lasting convection cooling without fan

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Protection

with cleaning cover

Use conditions

Storage/transport temperature

-20...60 °C

Relative humidity (without condensation)

10...90 %

Identification

Composition

other

Main design line

KNX