



WMDP84N

20A Double Pole Switch with LED Indicator

Technical characteristics

Configuration

Switch mode	2pole
Antibacterial treatment	Yes

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Depth	32.8 mm
Insertion depth	21.9 mm
Height	86 mm
Width	86 mm

Materials

Colour of design line	white
Design lines special colours	white
Colour independent of design lines	white
Colour	white
Material	Urea-formaldehyde

Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

Equipment

Lighting	with control LED for ON
Heating switch	No

Safety

REACH conform	No
Halogen free	No

Identification

Appliance switch type	No
-----------------------	----