



WMGS22RBSW

20A 2 Way Retractive Switch Brushed Steel White Insert

Technical characteristics

Configuration

Switch mode	2pole
-------------	-------

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Rated current	20 A
---------------	------

Dimensions

Depth	24 mm
Insertion depth	13.1 mm
Height	59 mm
Width	25 mm

Equipment

Lighting	without lighting (cannot be illuminated)
----------	------------------------------------------

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions

Insert	insert white
--------	--------------

Identification

Appliance switch type	No
-----------------------	----