



WMPS12

## 10AX 1 Gang 2 Way Wall Switch

### Technical characteristics

#### Configuration

Switch mode 2 way, with loop terminal

#### Controls and indicators

Push-buttons No

#### Main electrical features

Frequency 50/60 Hz

Rated current 10 AX

#### Dimensions

Depth 24 mm

Insertion depth 12 mm

Height 86 mm

Width 86 mm

#### Materials

Colour of design line white

Design lines special colours white

Colour independent of design lines white

Colour white

#### Installation, mounting

Installation mode for flush-mounted and hollow-wall mounting

#### Connection

Conductor cross-section 2 x 4 mm<sup>2</sup>

Terminal unique patented loop terminal allows neutral looping at the switch

#### Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

#### Equipment

Lighting without lighting (cannot be illuminated)

#### Standards

Standard BS EN 60669-1

#### Safety

REACH conform Yes

RoHS conform Yes

