



WMSS81

## 1 Gang Double Pole Switched Socket

### Technical characteristics

#### Functions

Overvoltage protection	No
------------------------	----

#### Configuration

Number of modules	0
-------------------	---

#### Main electrical features

Nominal voltage	250 V AC
Rated current	13 A

#### Dimensions

Depth	26 mm
Height	86 mm
Width	86 mm

#### Cover, door

Cover	Full cover plate
-------	------------------

#### Power supply

Special power supply	No special power supply
----------------------	-------------------------

#### Materials

Colour of design line	white
Design lines special colours	white
Colour independent of design lines	white
Colour	white
Type of surface treatment	untreated

#### Installation, mounting

Fixing type	With screws
Installation mode	for flush-mounted and hollow-wall mounting ; for screw fastening

#### Connection

Type of connection	screw
--------------------	-------

#### Cable

Wiring	with earth connection
--------	-----------------------

#### Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

**Equipment**

---

Number of socket outlets switchable	1
-------------------------------------	---

**Use**

---

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

**Safety**

---

IK protection code against mechanical impacts	sonstige
---	----------

---

REACH conform	Yes
---------------	-----

---

RoHS conform	Yes
--------------	-----

---

Halogen free	No
--------------	----

---

Protection	Enhanced contact protection
------------	-----------------------------