



WMSS81

1 Gang Double Pole Switched Socket

Technical characteristics

Functions

Overvoltage protection	No
------------------------	----

Configuration

Number of modules	0
-------------------	---

Main electrical features

Nominal voltage	250 V AC
Rated current	13 A

Dimensions

Depth	26 mm
Height	86 mm
Width	86 mm

Cover, door

Cover	Full cover plate
-------	------------------

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

Colour of design line	white
Design lines special colours	white
Colour independent of design lines	white
Colour	white
Type of surface treatment	untreated

Installation, mounting

Fixing type	With screws
Installation mode	for flush-mounted and hollow-wall mounting ; for screw fastening

Connection

Type of connection	screw
--------------------	-------

Cable

Wiring	with earth connection
--------	-----------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

Equipment

Number of socket outlets switchable	1
-------------------------------------	---

Use

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

Safety

IK protection code against mechanical impacts	sonstige
---	----------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Protection	Enhanced contact protection
------------	-----------------------------