



WMSS81

1 Gang Double Pole Switched Socket

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

Overvoltage protection No

Configuration

Number of modules 0

Main electrical features

Nominal voltage 250 V AC

Rated current 13 A

Dimensions

Depth 26 mm

Height 86 mm

Width 86 mm

Cover, door

Cover Full cover plate

Power supply

Special power supply No special power supply

Materials

Colour of design line white

Colour independent of design lines white

Colour white

Type of surface treatment untreated

Installation, mounting

Installation mode for flush-mounted and hollow-wall mounting, for screw fastening

Connection

Type of connection screw

Equipment

Number of socket outlets switchable 1

Use

Differentiation characteristic 3 - Sales with screw terminals

Safety

Protection index IP

IP20

Protection

Enhanced contact protection