



WMSS81-ME

1 Gang Double Pole Switched Socket

Technical characteristics

Functions

Overvoltage protection No

Configuration

Number of modules 0

Main electrical features

Nominal voltage 250 V

Rated voltage 220...230 V AC

Rated current 13 A

Dimensions

Depth 26 mm

Height 86 mm

Width 86 mm

Cover, door

Cover Full cover plate

Power supply

Special power supply No special power supply

Materials

Colour of design line white

Design lines special colours white

Colour independent of design lines white

Colour white

Surface appearance glossy

Type of surface treatment untreated

Installation, mounting

Fixing type With screws

Installation mode for flush-mounted and hollow-wall mounting ; for screw fastening

Connection

Type of connection screw

Cable

Wiring with earth connection

Scope of delivery

Equipment

Number of socket outlets switchable 1

Use

Differentiation characteristic 3 - Sales with screw terminals

Standards

Approvals NFC 61314

Safety

IK protection code against mechanical impacts sonstige

Protection Enhanced contact protection