



WMSS82

2 Gang Double Pole Switched Socket Dual Earth

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

Overvoltage protection	No
------------------------	----

Configuration

Number of modules	0
-------------------	---

Main electrical features

Nominal voltage	250 V AC
Rated current	13 A

Electric current

Rated current	13 A
---------------	------

Dimensions

Depth	29.5 mm
Height	86 mm
Width	146 mm

Cover, door

Cover	Full cover plate
-------	------------------

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

Colour	white
Surface appearance	matt
Type of surface treatment	untreated
Metallic colour	No

Installation, mounting

Fixing type	With screws
Installation mode	for flush-mounted and hollow-wall mounting, for screw fastening

Connection

Type of connection	screw
--------------------	-------

Equipment

Number of socket outlets switchable	0
Safety	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection