



WMSS82-ME

2 Gang Double Pole Switched Socket Dual Earth

Technical characteristics

Functions

Overvoltage protection	No
------------------------	----

Configuration

Number of modules	0
-------------------	---

Main electrical features

Nominal voltage	250 V
-----------------	-------

Rated voltage	220...230 V AC
---------------	----------------

Rated current	13 A
---------------	------

Electric current

Rated current	13 A
---------------	------

Dimensions

Depth	29.5 mm
-------	---------

Height	86 mm
--------	-------

Width	146 mm
-------	--------

Cover, door

Cover	Full cover plate
-------	------------------

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

Colour	white
--------	-------

Surface appearance	glossy
--------------------	--------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Fixing type	With screws
-------------	-------------

Installation mode	for flush-mounted and hollow-wall mounting ; for screw fastening
-------------------	--

Connection

Type of connection	screw
--------------------	-------

Cable

Wiring	with double earth connection
--------	------------------------------

Scope of delivery

Component

with 2 fixing screws M3.5 x 30 mm

Equipment

Number of socket outlets switchable

0

Safety

IK protection code against mechanical impacts

sonstige

Protection

Enhanced contact protection