



WMSS820G

2 Gang Double Pole Switched Socket Dual Earth Outboard Rockers Grey Face Plate

Technical characteristics

Functions

Overvoltage protection	No
------------------------	----

Configuration

Number of modules	0
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	13 A

Electric current

Rated current	13 A
---------------	------

Dimensions

Depth	29.5 mm
Height	86 mm
Width	146 mm

Cover, door

Cover	Full cover plate
-------	------------------

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

Surface appearance	glossy
Type of surface treatment	untreated
Metallic colour	No

Installation, mounting

Fixing type	With screws
Installation mode	for flush-mounted and hollow-wall mounting ; for screw fastening

Connection

Type of connection	screw
--------------------	-------

Cable

Wiring	with double earth connection
--------	------------------------------

Scope of delivery

Component

with 2 fixing screws M3.5 x 30 mm

Equipment

Number of socket outlets switchable

0

Safety

IK protection code against mechanical impacts

sonstige

Protection

Enhanced contact protection