



WMSSU83

### 13A FCU Switched

#### Technical characteristics

##### Configuration

Switch mode	2pole
Antibacterial treatment	No

##### Controls and indicators

Push-buttons	No
--------------	----

##### Main electrical features

Frequency	50/60 Hz
Rated current	13 A

##### Fuse

Fuse	with ceramic fine fuse F 13A
Fuse Size	6,3 x 25

##### Dimensions

Depth	30.3 mm
Insertion depth	25.3 mm
Height	86 mm
Width	86 mm

##### Materials

Colour of design line	white
Design lines special colours	white
Colour independent of design lines	white
Colour	white

##### Installation, mounting

Installation mode	for flush-mounted and hollow-wall mounting
-------------------	--

##### Connection

Conductor cross-section	max. 2 x 6 mm <sup>2</sup>
-------------------------	----------------------------

##### Cable

Wiring	with double earth connection
--------	------------------------------

##### Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

##### Equipment

Lighting	without lighting (cannot be illuminated)
----------	--

**Standards**

---

Standard

BS 1363-4

**Safety**

---

Protection

to protect downstream loads

**Identification**

---

Appliance switch type

No