



WMSSU83FO

13A FCU Switched with Flex Outlet

Technical characteristics

Architecture

Cable outlet with cable outlet

Configuration

Switch mode 2pole

Antibacterial treatment No

Controls and indicators

Push-buttons No

Main electrical features

Frequency 50/60 Hz

Rated current 13 A

Fuse

Fuse with ceramic fine fuse F 13A

Fuse Size 6,3 x 25

Dimensions

Depth 30.3 mm

Insertion depth 25.3 mm

Height 86 mm

Width 86 mm

Materials

Colour of design line white

Design lines special colours white

Colour independent of design lines white

Colour white

Installation, mounting

Installation mode for flush-mounted and hollow-wall mounting

Connection

Conductor cross-section max. 2 x 6 mm²

Cable

Wiring with double earth connection

Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

Equipment

Lighting without lighting (cannot be illuminated)

Standards

Standard BS 1363-4

Safety

Protection to protect downstream loads

Identification

Appliance switch type No