



WMSSU83FON

### 13A FCU Switched with LED Indicator and Flex Outlet

#### Technical characteristics

##### Architecture

Cable outlet with cable outlet

##### Configuration

Switch mode 2pole

Antibacterial treatment No

##### Controls and indicators

Push-buttons No

##### Main electrical features

Frequency 50/60 Hz

Rated current 13 A

##### Dimensions

Depth 30.3 mm

Insertion depth 25.3 mm

Height 86 mm

Width 86 mm

##### Materials

Colour of design line white

Colour independent of design lines white

Colour white

##### Installation, mounting

Installation mode for flush-mounted and hollow-wall mounting

##### Connection

Conductor cross-section max. 2 x 6 mm<sup>2</sup>

##### Equipment

Lighting with control LED for ON

##### Safety

Protection to protect downstream loads

##### Identification

Appliance switch type No