



WMSSU83FON

**13A FCU Switched with LED Indicator and Flex Outlet**

**Technical characteristics**

**Architecture**

Cable outlet with cable outlet

**Configuration**

Switch mode 2pole

Antibacterial treatment No

**Controls and indicators**

Push-buttons No

**Main electrical features**

Frequency 50/60 Hz

Rated current 13 A

**Fuse**

Fuse with ceramic fine fuse F 13A

Fuse Size 6,3 x 25

**Dimensions**

Depth 30.3 mm

Insertion depth 25.3 mm

Height 86 mm

Width 86 mm

**Materials**

Colour of design line white

Design lines special colours white

Colour independent of design lines white

Colour white

**Installation, mounting**

Installation mode for flush-mounted and hollow-wall mounting

**Connection**

Conductor cross-section max. 2 x 6 mm<sup>2</sup>

**Cable**

Wiring with double earth connection

**Scope of delivery**

Component with 2 fixing screws M3.5 x 30 mm

---

**Equipment**

Lighting

with control LED for ON

---

**Standards**

Standard

BS 1363-4

---

**Safety**

Protection

to protect downstream loads

---

**Identification**

Appliance switch type

No