



WPPS16

## Intermediate Switch

### Technical characteristics

#### Configuration

|             |              |
|-------------|--------------|
| Switch mode | intermediate |
|-------------|--------------|

#### Controls and indicators

|              |    |
|--------------|----|
| Push-buttons | No |
|--------------|----|

#### Main electrical features

|               |          |
|---------------|----------|
| Frequency     | 50/60 Hz |
| Rated current | 20 A     |

#### Dimensions

|                 |         |
|-----------------|---------|
| Depth           | 24 mm   |
| Insertion depth | 10.8 mm |
| Height          | 86 mm   |
| Width           | 86 mm   |

#### Materials

|                                    |       |
|------------------------------------|-------|
| Colour of design line              | grey  |
| Colour independent of design lines | Grey  |
| Colour                             | grey  |
| Material                           | Steel |

#### Connection

|                         |                       |
|-------------------------|-----------------------|
| Conductor cross-section | 2 x 4 mm <sup>2</sup> |
|-------------------------|-----------------------|

#### Equipment

|          |  |
|----------|--|
| Lighting | without lighting (cannot be illuminated) |
|----------|--|

#### Identification

|                       |    |
|-----------------------|----|
| Appliance switch type | No |
|-----------------------|----|