



WXD000B

Rocker switch gallery 2 modules pure-white

Technical characteristics

	Architecture
Clipped	Fixing mode
	Dimensions
8 mm	Depth
44.6 mm	Height
44.7 mr	Width
	Capacity
1	Number of sockets
	Materials
white	Colour
glossy	Surface appearance
untreated	Type of surface treatment
	Equipment
No	With transparent product label holder
	Standards
not concerne	European directive WEEE
	Safety
05	IK protection code against mecanical impacts
Yes	REACH conform
Yes	RoHS conform
Yes	Halogen free
	Use conditions
-1035 °C	Operating temperature
-1050 °C	Storage/transport temperature
	Identification
gallery	Range
other	Composition