



WXD202B

**Rocker for RJ45 socket gallery 2 modules pure-white**

**Technical characteristics**

**Architecture**

|             |              |
|-------------|--------------|
| Type        | Modular Jack |
| Fixing mode | Clipped      |

**Connectivity**

|        |                      |
|--------|----------------------|
| Outlet | with straight outlet |
|--------|----------------------|

**Dimensions**

|        |        |
|--------|--------|
| Depth  | 8.4 mm |
| Height | 45 mm  |
| Width  | 45 mm  |

**Capacity**

|                   |   |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

**Materials**

|                              |           |
|------------------------------|-----------|
| Free area for finishing name | pure      |
| Colour                       | white     |
| Surface appearance           | glossy    |
| Type of surface treatment    | untreated |

**Equipment**

|                                    |                         |
|------------------------------------|-------------------------|
| Supporting plate / Supporting ring | without supporting ring |
|------------------------------------|-------------------------|

**Standards**

|                         |               |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

**Safety**

|   |     |
|---|-----|
| IK protection code against mechanical impacts | 05  |
| REACH conform                                 | Yes |
| RoHS conform                                  | Yes |
| Halogen free                                  | Yes |

**Use conditions**

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

**Identification**

|                    |                          |
|--------------------|--------------------------|
| Application, usage | Communication technology |
| Range              | gallery                  |

Composition

other

With imprint

No