



WXF001

## 2 way switch gallery 2 modules

### Technical characteristics

#### Architecture

Type of order	Switch
Type of control unit	single rocker
Fixing mode	Clipped

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

#### Electric current

Rated current	10 AX
---------------	-------

#### Dimensions

Depth	34 mm
Insertion depth	34 mm
Height	45 mm
Width	45 mm

#### Materials

Surface appearance	matt
Type of surface treatment	untreated

#### Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 2,5mm <sup>2</sup>
Type of connection	Quickconnect

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

Approvals	EN 60669-1
-----------	------------

#### Safety

IK protection code against mechanical impacts	05
---	----

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

---

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

---

**Identification**

Range	gallery
Composition	Middle plate