



WXF112

## USB charger gallery

### Technical characteristics

#### Connectivity

Connectors / jacks with 2 USB sockets type A

#### Main electrical features

Rated voltage	200...250 V
Efficiency at low load (10 %)	74.1 %
Average active efficiency	83.3 %
Frequency	50/60 Hz

#### Voltage

Input voltage	230 V AC
Output voltage	5 V

#### Electric current

Output current	max. 3 A
----------------	----------

#### Fuse

Fuse short-circuit and overload proof (electronic fuse)

#### Power

Output power	15 W
No-load power consumption	71 mW

#### Materials

RAL colour RAL 7021 - Black grey

#### Use conditions

Operating temperature -5...35 °C

#### Instructions

Information text No data transmission possible!