



WXF160N

Schuko socket gallery 2P+E night

Technical characteristics

Architecture

Type of order	Socket
Type of pole	SCHUKO
Fixing mode	Clipped

Configuration

Number of modules	6
-------------------	---

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	40.25 mm
Height	45 mm
Width	45 mm

Cover, door

Cover	Complete housing
-------	------------------

Materials

Free area for finishing name	night
Surface appearance	satin finish
Metallic colour	No

Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm ²
Connection cross-sect. rigid cable	1,5 / 2,5mm ²
Type of connection	Quickconnect

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	VDE
-----------	-----

Safety

IK protection code against mechanical impacts	05
---	----

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection
Use conditions	
Operating temperature	-10...35 °C
Identification	
Range	gallery
Composition	Mechanism with upper casing