



WXF160R

## Schuko socket gallery 2P+E red

### Technical characteristics

#### Architecture

Fixing mode Clipped

#### Configuration

Number of modules 6

#### Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

#### Electric current

Rated current 16 A

#### Dimensions

Depth 40.25 mm

Height 45 mm

Width 45 mm

#### Cover, door

Cover Complete housing

#### Materials

Free area for finishing name red

Type of surface treatment untreated

Metallic colour No

#### Connection

Type of connection Quickconnect

#### Equipment

With transparent product label holder No

#### Standards

European directive WEEE concerned

#### Safety

IK protection code against mechanical impacts 05

Protection Enhanced contact protection

#### Use conditions

Operating temperature -10...35 °C

**Identification**

---

Range

gallery

---

Composition

Mechanism with upper casing