



WXF160R

**Schuko socket gallery 2P+E red**

**Technical characteristics**

**Architecture**

Type of order	Socket
Type of pole	SCHUKO
Fixing mode	Clipped

**Configuration**

Number of modules	6
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Depth	40.25 mm
Height	45 mm
Width	45 mm

**Cover, door**

Cover	Complete housing
-------	------------------

**Materials**

Free area for finishing name	red
Surface appearance	glossy
Type of surface treatment	untreated
Metallic colour	No

**Connection**

Connection cross-sect. flexible conductor	1,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 2,5mm <sup>2</sup>
Type of connection	Quickconnect

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

Approvals	VDE
-----------	-----

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection
<b>Use conditions</b>	
Operating temperature	-10...35 °C
<b>Identification</b>	
Range	gallery
Composition	Mechanism with upper casing