



WXF160V

**Schuko socket gallery 2P+E green**

**Technical characteristics**

**Architecture**

|               |         |
|---------------|---------|
| Type of order | Socket  |
| Type of pole  | SCHUKO  |
| Fixing mode   | Clipped |

**Configuration**

|                   |   |
|-------------------|---|
| Number of modules | 6 |
|-------------------|---|

**Main electrical features**

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Frequency       | 50/60 Hz |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

**Dimensions**

|        |          |
|--------|----------|
| Depth  | 40.25 mm |
| Height | 45 mm    |
| Width  | 45 mm    |

**Cover, door**

|       |                  |
|-------|------------------|
| Cover | Complete housing |
|-------|------------------|

**Materials**

|                              |           |
|------------------------------|-----------|
| Free area for finishing name | green     |
| Surface appearance           | glossy    |
| Type of surface treatment    | untreated |
| Metallic colour              | No        |

**Connection**

|   |                          |
|---|--------------------------|
| Connection cross-sect. flexible conductor | 1,5 / 2,5mm <sup>2</sup> |
| Connection cross-sect. rigid cable        | 1,5 / 2,5mm <sup>2</sup> |
| Type of connection                        | Quickconnect             |

**Equipment**

|                                       |    |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

**Standards**

|           |     |
|-----------|-----|
| Approvals | VDE |
|-----------|-----|

**Safety**

|   |                             |
|---|-----------------------------|
| IK protection code against mechanical impacts | 05                          |
| REACH conform                                 | Yes                         |
| RoHS conform                                  | Yes                         |
| Protection                                    | Enhanced contact protection |
| <b>Use conditions</b>                         |                             |
| Operating temperature                         | -10...35 °C                 |
| <b>Identification</b>                         |                             |
| Range   | gallery                     |
| Composition                                   | Mechanism with upper casing |