



WXF225

## RJ45 socket gallery cat.6 UTP

### Technical characteristics

#### Architecture

Type UTP

#### Connectivity

Outlet with straight outlet

#### Dimensions

Depth 34.6 mm

Height 45 mm

Width 45 mm

#### Capacity

Number of sockets 1

#### Materials

Surface appearance matt

#### Connection

Connection cross-sect. rigid cable 0,5 - 0,65 mm<sup>2</sup>

Connector type shielding connection via Clip

#### Cable

AWG range AWG 26-22

#### Safety

IK protection code against mechanical impacts IK02

REACH conform Yes

RoHS conform Yes

Protection with optional dust protection hinged covers

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Application, usage Communication technology

Range gallery

Composition Middle plate