



WXF226

## RJ45 socket gallery cat.6 STP

### Technical characteristics

#### Architecture

Type	STP
------	-----

#### Connectivity

Outlet	with straight outlet
--------	----------------------

#### Dimensions

Depth	34.6 mm
-------	---------

Height	45 mm
--------	-------

Width	45 mm
-------	-------

#### Attenuation

Transmission loss	3 dB
-------------------	------

#### Capacity

Number of sockets	1
-------------------	---

#### Materials

Surface appearance	matt
--------------------	------

#### Connection

Connection cross-sect. rigid cable	0,5 - 0,65 mm <sup>2</sup>
------------------------------------	----------------------------

Connector type	shielding connection via Clip
----------------	-------------------------------

#### Cable

AWG range	AWG 26-22
-----------	-----------

#### Safety

IK protection code against mechanical impacts	IK02
---	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Protection	with optional dust protection hinged covers
------------	---

#### Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

#### Identification

Application, usage	Communication technology
--------------------	--------------------------

Range	gallery
-------	---------

Composition	Middle plate
-------------	--------------