



WXF258

TV socket gallery type F direct 2 modules

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Connectivity

Passband	4 - 2400 MHz
----------	--------------

Dimensions

Depth	34 mm
Height	45 mm
Width	45 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Material	Plastic/metal
Surface appearance	matt
Type of surface treatment	untreated

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	IK02
Protection index IP	IP20

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	Middle plate