



WXF300

Switch for shutter gallery 1 way 2 modules

Technical characteristics

Architecture

| | |
|----------------------|---------------|
| Type of control unit | double rocker |
| Fixing mode | Clipped |

Compatibility

| | |
|-------------------------|----|
| IFTTT support available | No |
|-------------------------|----|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Frequency | 50/60 Hz |

Electric current

| | |
|---------------|-------|
| Rated current | 10 AX |
|---------------|-------|

Dimensions

| | |
|--------|-------|
| Depth | 34 mm |
| Height | 45 mm |
| Width | 45 mm |

Materials

| | |
|---------------------------|----------------------|
| Colour | dark grey |
| RAL colour | RAL 7011 - Iron grey |
| Surface appearance | matt |
| Type of surface treatment | untreated |

Connection

| | |
|--------------------|--------------|
| Type of connection | Quickconnect |
|--------------------|--------------|

Equipment

| | |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---|----|
| IK protection code against mechanical impacts | 05 |
|---|----|

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

Identification

Range

gallery

Composition

Middle plate