



WXF625

Speaker socket gallery

Technical characteristics

Connectivity

Outlet	with straight outlet
--------	----------------------

Dimensions

Depth	41.5 mm
Height	45 mm
Width	45 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Surface appearance	mat
Type of surface treatment	untreated

Safety

IK protection code against mechanical impacts	IK02
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	Middle plate