



WXF625

Speaker socket gallery

Technical characteristics

Architecture

Fixing mode flush-mounting

Connectivity

Outlet with straight outlet

Dimensions

Depth 41.5 mm

Height 45 mm

Width 45 mm

Capacity

Number of sockets 1

Materials

Surface appearance matt

Type of surface treatment untreated

Standards

European directive WEEE concerned

Safety

IK protection code against mechanical impacts IK02

Protection index IP IP20

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Middle plate