



WXF688B

**Blank function gallery 1 module pure-white**

**Technical characteristics**

**Architecture**

Fixing mode Clipped

**Dimensions**

Depth 29.5 mm

Height 45 mm

Width 22.5 mm

**Materials**

Free area for finishing name pure

Colour white

Surface appearance glossy

Type of surface treatment untreated

**Standards**

European directive WEEE not concerned

**Safety**

IK protection code against mechanical impacts IK02

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

**Identification**

Range gallery

Composition other

With imprint No