



WXF688B

Blank function gallery 1 module pure-white

Technical characteristics

Architecture

Fixing mode Clipped

Dimensions

Depth 29.5 mm

Height 45 mm

Width 22.5 mm

Materials

Free area for finishing name pure

Colour white

Surface appearance glossy

Type of surface treatment untreated

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts IK02

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition other

With imprint No